

Gaminio duomenų lentelė

Savybės

13168

Kaedra - versatile for power outlet - 1 x 18+1
modules - 448 x 460 mm



Main

Range	Kaedra
Product or component type	Weatherproof enclosure
Enclosure type	Versatile enclosure for power outlet
Mounting plate description	Without mounting plate

Complementary

Enclosure mounting	Surface
Number of 18 mm modules per row	18
Total number of 18 mm modules	18
Number of horizontal rows	1
Electrical insulation class	Double insulation Class II
Type of front cover	Transparent
Power dissipation in W	28 W
[In] rated current	90 A
Type of rail	DIN
Number of pre-cutouts PG ISO	17
Locking options description	Optional keylock
Enclosure material	self-extinguishing polymer
Width	448 mm
Height	460 mm
Depth	160 mm
Internal depth	91 mm
Colour	Door transparent green Enclosure light grey RAL 7035)
Targeted country	France

Environment

Standards	EN 50102 IEC 60439-3 IEC 60529
-----------	--------------------------------------

IEC 670
EN 50262

Fire resistance	750 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 IEC 60529
IK degree of protection	IK09 EN 50102
Environmental characteristics (UV)	UV resistant class 3ISO 4582:2010 Ultraviolet degradation testISO 4892-2:2013
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C

Packing Units

1-os pakuotės vieneto tipas	PCE
Vienetų skaičius 1-oje pakuotėje	1
1 pakuotės svoris	3,43 kg
1 pakuotės aukštis	17,8 cm
1 pakuotės plotis	46,8 cm
1 pakuotės ilgis	47 cm
2 pakuotės vieneto tipas	P12
Vienetų skaičius 2-oje pakuotėje	18
2 pakuotės svoris	73,74 kg
2 pakuotės aukštis	80 cm
2 pakuotės plotis	80 cm
2 pakuotės ilgis	120 cm

Offer Sustainability

REACH direktyva	REACH deklaracija
ES RoHS direktyva	Aktyvus laikymasis (gaminys nepatenka į ES RoHS teisinę aprėptį) ES RoHS deklaracija
Be gyvsidabrio	Taip
RoHS išimčių informacija	Taip
Kinijos RoHS direktyva	Kinijos RoHS deklaracija Produktas neįeina į Kinijos RoHS apimtį. Medžiagų deklaracija pateikiama jūsų informacijai.

Contractual warranty

Garantija	18 months
-----------	-----------