

Gaminio duomenų lentelė

Savybės

33442

basic switch disconnector, Compact NS800 NA, fixed, electrically operated, 800 A, 690 VAC 50/60 Hz, 3 poles



Main

Product name	ComPact NS
Device short name	Compact NS800 NA
Product or component type	Switch disconnector
Device application	Distribution
Offer type	C4
Poles description	3P
Network type	AC
Performance level	NA
Suitability for isolation	Yes IEC 60947-3

Complementary

Network frequency	50/60 Hz
Control type	Motor mechanism
Mounting mode	Fixed
Mounting support	Chassis
[Ie] rated operational current	AC-23A 800 A AC 50/60 Hz 220/240 V AC-23A 800 A AC 50/60 Hz 380/415 V AC-23A 800 A AC 50/60 Hz 440/480 V AC-23A 800 A AC 50/60 Hz 500/525 V AC-23A 800 A AC 50/60 Hz 660/690 V
[Ui] rated insulation voltage	1000 V AC 50/60 Hz conforming to IEC 60947-3
[Uimp] rated impulse withstand voltage	8 kV IEC 60947-3
[Ith] conventional free air thermal current	800 A 60 °C
[Icw] rated short-time withstand current	25 kA 0.5 s IEC 60947-3 4 kA 20 s IEC 60947-3
[Icm] rated short-circuit making capacity	52 kA 690 V AC 50/60 Hz
[Ue] rated operational voltage	690 V AC 50/60 Hz IEC 60947-3
Contact position indicator	Yes
Visible break	No

Mechanical durability	6000 cycles IEC 60947-3
Electrical durability	1000 cycles 440 V AC 50/60 Hz IEC 60947-3
Connection pitch	70 mm
Height	327 mm
Width	210 mm
Depth	147 mm
Net weight	14 kg

Environment

Standards	IEC 60947-3
Product certifications	ASTA ASEFA
Pollution degree	3 IEC 60947-3
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Packing Units

1 pakuotės svoris	11,738 kg
1 pakuotės aukštis	3,600 dm
1 pakuotės plotis	2,300 dm
1 pakuotės ilgis	3,900 dm

Offer Sustainability

REACH direktyva	REACH deklaracija
ES RoHS direktyva	Atitinka ES RoHS deklaracija
Be gyvsidabrio	Taip
RoHS išimčių informacija	Taip
Kinijos RoHS direktyva	Kinijos RoHS deklaracija Produktas neįeina į Kinijos RoHS apimtį. Medžiagų deklaracija pateikiama jūsų informacijai.
WEEE	Šį produktą Europos Sąjungos rinkose reikia utilizuoti perduodant į specialias surinkimo vietas ir negalima išmesti su buitinėmis atliekomis.
Be PVC	Taip

Contractual warranty

Garantija	18 months
-----------	-----------