



Main

Range	Wibe
Range of product	Wibe Cable Trays
Product or component type	T-junction
Device short name	W12
Mounting location	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Complementary

Operating angle	90 °
Direction change type	Horizontal
Product destination	Cable tray 40 mm 500 mm
Mounting mode	Push-in
Fixing mode	By locking plug By bolt
Material with surface treatment	Steel, pre-galvanized
Corrosion class	C2
Width	597 mm
Depth	697 mm
Net weight	438 kg / set of 100

Packing Units

1 pakuočių svoris	4380,000 g
-------------------	------------

Offer Sustainability

Tvaraus pasiūlymo statusas	„Green Premium“ gaminys
REACH direktyva	REACH deklaracija
REACH be SVHC	Taip

ES RoHS direktyva	Aktyvus laikymasis (gaminys nepatenka į ES RoHS teisinę aprėptį) ES RoHS deklaracija
Be sunkių toksiškų metalų	Taip
Be gyvsidabrio	Taip
RoHS išimčių informacija	Taip
Kinijos RoHS direktyva	Kinijos RoHS deklaracija Proaktyvi Kinijos RoHS deklaracija (neįeinanti į Kinijos RoHS teisinę apimtį)
Aplinkosauginės informacijos atskleidimas	Produkto aplinkosaugos profilis

Contractual warranty

Garantija	18 months
-----------	-----------