



### Main

Range	Wibe
Product name	Wibe Cable Ladders
Product or component type	Cable ladder
Device short name	KHZP
Device application	Industrial application

### Complementary

Type of side profile	Closed profile
Type of rung	Perforated profile
Mounting location	Outdoor Indoor
Rung spacing	250 mm
Material with surface treatment	Stainless steel AISI 316L
Corrosion class	C5-M
Height	55 mm
Width	150 mm
Length	6 m
Net weight	260 kg / 100 m

### Environment

Mounting location	Area with almost permanent high levels of humidity, airborne pollution and salt purify-ing plants and offshore
Standards	IEC 61537

### Packing Units

1-os pakuotės vieneto tipas	PCE
-----------------------------	-----

Vienetų skaičius 1-oje pakuotėje	1
1 pakuotės svoris	13,3 kg
1 pakuotės aukštis	5,5 cm
1 pakuotės plotis	14,7 cm
1 pakuotės ilgis	600 cm

### Offer Sustainability

Tvaraus pasiūlymo statusas	„Green Premium“ gaminys
REACH direktyva	<a href="#">REACH deklaracija</a>
REACH be SVHC	Taip
ES RoHS direktyva	Aktyvus laikymasis (gaminys nepatenka į ES RoHS teisinę aprėptį) <a href="#">ES RoHS deklaracija</a>
Be sunkių toksiškų metalų	Taip
Be gyvsidabrio	Taip
RoHS išimčių informacija	<a href="#">Taip</a>
Kinijos RoHS direktyva	<a href="#">Kinijos RoHS deklaracija</a> Proaktyvi Kinijos RoHS deklaracija (nejeinanti į Kinijos RoHS teisinę apimtį)
Aplinkosauginės informacijos atskleidimas	<a href="#">Produkto aplinkosaugos profilis</a>

### Contractual warranty

Garantija	18 months
-----------	-----------