

Gaminio duomenų lentelė

Savybės

753CF2

Motion Sensor Infrascan - Passive infrared -
Indoor - Two-channel - 3.5m detection radius -
240 V



Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	LED lighting 100 W Compact fluorescent lamp 100 W Motor 100 W Relay 5 A - 250 V Incandescent lamps 1000 W - 230 V Halogen lamp 900 W - 230 V Halogen lamp with standard electronic transformer 250 VA Halogen lamp with standard ferromagnetic transformer 500 VA Capacitive 6 A, 21 µF Capacitive 10 A, 14 µF Fluorescent tube 200 VA
Colour tint	White

Complementary

Network frequency	50/60 Hz
Input function	Switch
Output voltage	220...250 V
Output current	10 A
Number of channels	2
Control type	Movement sensor
Function available	Switching, toggling, dimming
Light intensity adjustment	5...1000 lux
Horizontal detection angle	360 °
Cable length	0,035 m
Detection range	Radius 3500 mm

Mounting height	2,5 m
-----------------	-------

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

1 pakuotės svoris	207,000 g
1 pakuotės aukštis	60,000 mm
1 pakuotės plotis	125,000 mm
1 pakuotės ilgis	125,000 mm

Offer Sustainability

Tvaraus pasiūlymo statusas	„Green Premium“ gaminys
REACH direktyva	REACH deklaracija
REACH be SVHC	Taip
ES RoHS direktyva	Atitinka ES RoHS deklaracija
Be sunkių toksiškų metalų	Taip
Be gyvsidabrio	Taip
RoHS išimčių informacija	Taip
Kinijos RoHS direktyva	Kinijos RoHS deklaracija Proaktyvi Kinijos RoHS deklaracija (nejeinanti į Kinijos RoHS teisinę apimtį)
Aplinkosauginės informacijos atskleidimas	Produkto aplinkosaugos profilis
WEEE	Šį produktą Europos Sąjungos rinkose reikia utilizuoti perduodant į specialias surinkimo vietas ir negalima išmesti su buitinėmis atliekomis.