



Main

Range	PowerLogic
Product name	ComX
Product or component type	Energy server
Device short name	ComX 210

Complementary

[Us] rated supply voltage	Main supply 24 V DC
Maximum power consumption in W	26 W 24 V 15 W via PoE
Communication network type	RS485, Modbus serial 1 RJ45 RS485, Modbus serial terminal block Ethernet, PoE 15W (Power over Ethernet) 1 RJ45 Ethernet, DHCP 1 RJ45
Number of inputs	6 digital 2 analog
Discrete input current	60 mA 12 V DC
Sensor power supply	24 V DC 50 mA
Analogue input type	4...20 mA Pt 100 Pt 1000 0...10 V
Communication gateway	Ethernet TCP/IP to Modbus
Memory capacity	128 MB RAM 256 MB flash
Mounting mode	Clip-on
Mounting support	35 mm DIN rail
Product certifications	CE CUL C-Tick UL
Standards	EN 61010-1 UL 508 EN 60950 UL 60950
Depth	69 mm

Height	109 mm
Width	144 mm
Net weight	450 g
Local signalling	LED:power supply LED:status GPRS) LED:communication Modbus) LED:communication Ethernet) LED:communication WiFi) LED:I/O

Environment

Relative humidity	5...95 % 55 °C without condensation
IP degree of protection	IP20 terminal block) IP40 front face)
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Pollution degree	3
Operating altitude	2000 m

Packing Units

1-os pakuotės vieneto tipas	PCE
Vienetų skaičius 1-oje pakuotėje	1
1 pakuotės svoris	419 g
1 pakuotės aukštis	8 cm
1 pakuotės plotis	11 cm
1 pakuotės ilgis	16 cm
2 pakuotės vieneto tipas	S03
Vienetų skaičius 2-oje pakuotėje	15
2 pakuotės svoris	6,772 kg
2 pakuotės aukštis	30 cm
2 pakuotės plotis	30 cm
2 pakuotės ilgis	40 cm

Offer Sustainability

REACH direktyva	REACH deklaracija
REACH be SVHC	Taip
ES RoHS direktyva	Atitinka ES RoHS deklaracija
Be sunkių toksiškų metalų	Taip
Be gyvsidabrio	Taip
RoHS išimčių informacija	Taip
Kinijos RoHS direktyva	Kinijos RoHS deklaracija
WEEE	Šį produktą Europos Sąjungos rinkose reikia utilizuoti perduodant į specialias surinkimo vietas ir negalima išmesti su buitinėmis atliekomis.