


Gaminio duomenų lentelė

Specifikacijos



gearbox with straight teeth GBX- Ø 60 mm- reduction 60:1- < 22arcmin- 44 N.m

GBX0600600703F

⚠ Pranešimo apie gaminio gamybos nutraukimą data 2022-03-31

⚠ Nutraukta

Pagrindinis

Diapazono Suderinamumas	Lexium 32
Produkto Arba Komponento Tipas	Planetary gearbox
Gear Box Type	Straight teeth
Trumpasis Įrenginio Pavadinimas	GBX
Gearbox External Diameter	60 mm
Product Compatibility	BSH0703... BMH0703...
Reduction Ratio	60:1

Papildoma

Maximum Torsional Backlash	22 arc.min
Torsional Rigidity	2.5 N.m/arcmin
Housing Colour	Black
Housing Material	Black anodized aluminium
Shaft Material	C 45
Additional Information	Lubricated for life
Service Life In Hours	30000 h 100 rpm 30 °C
Efficiency	94 %
Maximum Radial Force Fr	340 N 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 °C 500 N 100 rpm, force applied at mid-distance from output shaft during 10000 hour at 30 °C
Maximum Axial Force Fa	450 N 100 rpm, during 30000 hour at 30°C 600 N 100 rpm, during 10000 hour at 30°C
Continuous Output Torque	44 N.m 100 rpm 30 °C
Maximum Output Torque	70 N.m 100 rpm 30 °C
Grynasis Svoris	1,3 kg

Aplinka

Noise Level	58 dB 1 m, no-load
Ip Degree Of Protection	Shaft output IP54
Ambient Temperature For Operation	-25...90 °C

Atsakomybės apribojimas. Šių dokumentų tikslas nėra nurodyti produktų tinkamumą tam tikram naudojimui ar nusiųsti jų patikimumą. Jie taip pat neatstoja tinkamumo ar patikimumo nustatymo

Sutartinė garantija

Garantija	18 months
-----------	-----------