



### Komercinis statusas

Nebegaminama nuo: 07 Balandžio 2020

Tarnavimo laiko pabaiga: 01 Liepos 2020

⚠ Nutraukta

### Main

Range of product	Harmony K
Product or component type	Cam switch body
Component name	K1
[Ith] conventional free air thermal current	12 A
Sub-assembly composition	Contact blocks + fixing plate
Cam switch function	Switch
Mounting location	Front
Fixing mode	Ø 22 mm hole
Bezel material	Plastic

### Complementary

[Ui] rated insulation voltage	690 V 3)IEC 60947-1
[Ithe] conventional enclosed thermal current	10 A
Rated operational power in W	10500 W AC-21, 500 - 660 V 3 phases IEC 947-3
[Ie] rated operational current AC	1 A 500 V AC-15 IEC 947-5-1
Electrical durability	1000000 cycles AC-15
Maximum operating rate	2,5 cyc/mn AC-21
Short-circuit current	10000 A
Short-circuit protection	20 A cartridge fuse gG
[Uimp] rated impulse withstand voltage	4 kV in isolating function
Contact operation	Slow-break
Positive opening	With
Electrical connection	Captive screw clamp terminals flexible 2 x 1.5 mm <sup>2</sup>
Mechanical durability	1000000 cycles

### Environment

Standards	CENELEC EN 50013
Product certifications	CSA 240 V 1 hp 1 phase
Protective treatment	TC

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...70 °C
Shock resistance	30 gn conforming to IEC 68-2-27
Vibration resistance	5 gn conforming to IEC 68-2-6 (f = 10...150 Hz)
Overvoltage category	Class II conforming to IEC 536
IP degree of protection	IP40 conforming to IEC 529

### Packing Units

1-os pakuotės vieneto tipas	PCE
Vienetų skaičius 1-oje pakuotėje	1
1 pakuotės svoris	130 g
1 pakuotės aukštis	8 cm
1 pakuotės plotis	6,5 cm
1 pakuotės ilgis	6,5 cm

### Offer Sustainability

REACH direktyva	<a href="#">REACH deklaracija</a>
REACH be SVHC	Taip
ES RoHS direktyva	Aktyvus laikymasis (gaminys nepatenka į ES RoHS teisinę aprėptį) <a href="#">ES RoHS deklaracija</a>
Be sunkių toksiškų metalų	Taip
Be gyvsidabrio	Taip
RoHS išimčių informacija	<a href="#">Taip</a>
Kinijos RoHS direktyva	<a href="#">Kinijos RoHS deklaracija</a>

### K1S5 pakeistas šios serijos produktais:



#### Harmony K

Paketiniai perjungikliai

Kumšteliniai (paketiniai) jungikliai, 16 ir 22 mm diametro