



### Main

Range	TeSys
Product name	TeSys LE
Device short name	LE3D
Product or component type	Enclosed star-delta starter
Device application	Standard
Material	Sheet steel
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Star-delta contactors Neutral terminal
Motor power kW	132 kW at 380/400 V AC 50/60 Hz 132 kW at 415 V AC 50/60 Hz 147 kW at 440 V AC 50/60 Hz 75 kW 220 V AC 50/60 Hz
[Uc] control circuit voltage	220 V AC 50/60 Hz
Control type	Without

### Complementary

Width	500 mm
Height	600 mm
Depth	252 mm
Net weight	24,5 kg

### Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

---

Garantija	18 months
-----------	-----------

---