



Main

Device short name	MX
Product or component type	Voltage release
Device application	Control
Range compatibility	ComPact NSX EasyPact CVS PowerPact Multistandard ComPact NSX DC
Voltage release type	Undervoltage release
[U _c] control circuit voltage	600 V AC 60 Hz 525 V AC 50 Hz

Complementary

Threshold tripping voltage	0.35...0.7 x U _n opening 0.85 x U _n closing
Supply holding power	5 VA
Supply inrush power	10 VA
Mounting mode	Fixed
Response time	50 ms
Auxiliary connection terminal	screw terminal 0...1,5 mm ²

Packing Units

1 pakuotės svoris	0,121 kg
1 pakuotės aukštis	0,640 dm
1 pakuotės plotis	0,400 dm
1 pakuotės ilgis	0,830 dm

Offer Sustainability

Tvaraus pasiūlymo statusas	„Green Premium“ gaminys
REACH direktyva	REACH deklaracija
ES RoHS direktyva	Atitinka ES RoHS deklaracija
Be gyvsidabrio	Taip
RoHS išimčių informacija	Taip
Kinijos RoHS direktyva	Kinijos RoHS deklaracija Produktas neįeina į Kinijos RoHS apimtį. Medžiagų deklaracija pateikiama jūsų informacijai.
Aplinkosauginės informacijos atskleidimas	Produkto aplinkosaugos profilis
WEEE	Šį produktą Europos Sąjungos rinkose reikia utilizuoti perduodant į specialias surinkimo vietas ir negalima išmesti su buitėmis atliekomis.

Contractual warranty

Garantija	18 months
-----------	-----------