



Apžvalga

Pristatymo laikas	Usually in Stock
-------------------	------------------

General

Provided equipment	All required connectors Battery recycling guide Reusable packaging Installation guide
--------------------	--

Physical

Colour	Black
Depth	18,3 cm
Height	17,3 cm
Net weight	24,27 kg
Width	14,2 cm

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0,00...15240,00 m
Storage Relative Humidity	0...95 %

Batteries & Runtime


Number of battery free slots	0
Number of battery filled slots	0
Battery type	Lead-acid battery

Number of battery replacement quantity	1
--	---

Packing Units

1 pakuotės svoris	26,68 kg
1 pakuotės aukštis	27,7 cm
1 pakuotės plotis	29,5 cm
1 pakuotės ilgis	53,8 cm
Vienetų skaičius 3-ioje pakuotėje	18

Offer Sustainability

Tvaraus pasiūlymo statusas	„Green Premium“ gaminys
Energy Star	ENERGY STAR UPS V1.0 (JAV) 
REACH direktyva	REACH deklaracija
ES RoHS direktyva	Aktyvus laikymasis (gaminys nepatenka į ES RoHS teisinę aprėptį) ES RoHS deklaracija
Aplinkosauginės informacijos atskleidimas	Produkto aplinkosaugos profilis
Žiedinės ekonomikos profilis	Eksplotavimo ciklo pabaigos informacija

Contractual warranty

Garantija	1 year repair or replace
-----------	--------------------------