



Main

Range	Prisma
Range compatibility	Prisma G
Product or component type	Rail
Accessory / separate part category	Installation accessory
Type of rail	Modular
Installed device	<p>Multi 9: fixed modular device Acti 9: fixed modular device Multi 9 : fixed modular device <= 40 A Acti 9 : fixed modular device <= 40 A Multi 9 : fixed NG125 without earth leakage protection - control: toggle Multi 9 : fixed NG125 with earth leakage protection Compact : fixed INS40 - control: direct front rotary handle - vertical installation Compact : fixed INS63 - control: direct front rotary handle - vertical installation Compact : fixed INS100 - control: direct front rotary handle - vertical installation Compact : fixed INS125 - control: direct front rotary handle - vertical installation Compact : fixed INS160 - control: direct front rotary handle - vertical installation Acti 9 : fixed iC120 with earth leakage protection - control: toggle Acti 9 : fixed iC120 without earth leakage protection - control: toggle</p>
Poles description	<p>12 x 2P : fixed : NG125 6 x 2P : fixed : NG125 8 x 3P : fixed : NG125 4 x 3P : fixed : NG125 6 x 4P : fixed : NG125 3 x 4P : fixed : NG125 24 x 1P : fixed : iC120 4 x 3P : fixed : INS40 vertical installation 4 x 3P : fixed : INS63 vertical installation 4 x 3P : fixed : INS100 vertical installation 4 x 3P : fixed : INS125 vertical installation 4 x 3P : fixed : INS160 vertical installation 6 x 4P : fixed : iC120 3 x 4P : fixed : iC120 4 x 4P : fixed : INS40 vertical installation 4 x 4P : fixed : INS63 vertical installation 4 x 4P : fixed : INS100 vertical installation 4 x 4P : fixed : INS125 vertical installation 4 x 4P : fixed : INS160 vertical installation 12 x 2P : fixed : iC120 8 x 3P : fixed : iC120</p>

Ir sasniegts maksimālais salīdzināmo produktu skaits. Lūdzu, atveriet sadalīto salīdzināt produktu #SAITE# un izdzesiet kādu produktu, lai turpinātu.

5 x 2P : fixed : iC120
3 x 3P : fixed : iC120

Complementary

Installation description	Floor-standing enclosure - width 850 mm
Number of vertical modules [50 mm]	5 module(s) : iC120 without earth leakage protection , direct in 850 mm Wide floor-standing enclosure 4 module(s) : INS100 , direct in 850 mm Wide floor-standing enclosure 5 module(s) : INS100 , direct in 850 mm Wide floor-standing enclosure 4 module(s) : INS125 , direct in 850 mm Wide floor-standing enclosure 5 module(s) : INS125 , direct in 850 mm Wide floor-standing enclosure 4 module(s) : INS160 , direct in 850 mm Wide floor-standing enclosure 5 module(s) : INS160 , direct in 850 mm Wide floor-standing enclosure 4 module(s) : INS40 , direct in 850 mm Wide floor-standing enclosure 4 module(s) : INS63 , direct in 850 mm Wide floor-standing enclosure 3 module(s) : modular device <= 40 A , direct in 850 mm Wide floor-standing enclosure 4 module(s) : modular device , direct in 850 mm Wide floor-standing enclosure 5 module(s) : NG125 without earth leakage protection , direct in 850 mm Wide floor-standing enclosure 5 module(s) : iC120 with earth leakage protection , direct in 850 mm Wide floor-standing enclosure 5 module(s) : NG125 with earth leakage protection , direct in 850 mm Wide floor-standing enclosure
9 mm pitches	72
Quantity per set	Set of 1
Height	35 mm
Width	662 mm
Depth	15 mm
Product weight	0.3 kg
Colour	Grey
Thickness	1.5 mm

Environment

Standards	IEC 61439-1 IEC 61439-2
-----------	----------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Produkta ietekme uz vidi
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------