



Main

| | |
|------------------------------------|--|
| Range | Prisma |
| Range compatibility | Prisma P Prisma G Pack 160 |
| Product or component type | Front plate |
| Accessory / separate part category | Installation accessory |
| Type of front plate | Cut-out Modular |
| Installed device | <p>TeSys: fixed GV3</p> <p>Multi 9 : fixed NG125 with earth leakage protection - control: toggle</p> <p>Multi 9 : fixed NG125 without earth leakage protection - control: toggle</p> <p>Multi 9 : fixed NG125 NA - control: toggle</p> <p>Acti 9 : fixed C120 with earth leakage protection - control: toggle</p> <p>Acti 9 : fixed C120 without earth leakage protection - control: toggle</p> <p>Compact : fixed NG160 with earth leakage protection - control: toggle</p> <p>Compact : fixed NG160 without earth leakage protection - control: toggle</p> <p>TeSys : fixed TeSys U - horizontal installation</p> <p>Compact : fixed INS100 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INS125 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INS160 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed NG160 NA without earth leakage protection - control: toggle</p> <p>Acti 9 : fixed iC120 with earth leakage protection - control: toggle</p> <p>Acti 9 : fixed iC120 without earth leakage protection - control: toggle</p> <p>Compact : fixed NSXm without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSXm with earth leakage protection - control: toggle - vertical installation</p> |
| Poles description | <p>9 x 3P : modular rail support : TeSys U horizontal installation</p> <p>1 x 3P : modular rail support : INS100 vertical installation</p> <p>1 x 4P : modular rail support : INS100 vertical installation</p> <p>1 x 3P : modular rail support : INS125 vertical installation</p> <p>1 x 4P : modular rail support : INS125 vertical installation</p> <p>1 x 3P : modular rail support : INS160 vertical installation</p> <p>1 x 4P : modular rail support : INS160 vertical installation</p> <p>1 x 3P : modular rail support : C120</p> <p>1 x 4P : modular rail support : C120</p> <p>7 x 3P : modular rail support : GV3</p> <p>1 x 3P : modular rail support : iC120</p> <p>1 x 4P : modular rail support : iC120</p> <p>1 x 3P : modular rail support : NG125</p> <p>1 x 4P : modular rail support : NG125</p> |

1 x 3P : modular rail support : NG125 NA
 1 x 4P : modular rail support : NG125 NA
 1 x 3P : modular rail support : NG160
 1 x 4P : modular rail support : NG160
 1 x 3P : modular rail support : NG160 NA
 1 x 4P : modular rail support : NG160 NA
 5 x 3P : mounting plate support : NSXm vertical installation
 4 x 4P : mounting plate support : NSXm vertical installation
 4 x 3P or 4P : mounting plate support : NSXm vertical installation
 1 x 3P or 4P : modular rail support : NSXm vertical installation

| | |
|--------------------|----------|
| Operating position | Vertical |
|--------------------|----------|

Complementary

| | |
|------------------------------------|---|
| Enclosure/Cubicle description | Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm, depth 400 mm Pack enclosure - width 555 mm |
| Connection position | Direct connection |
| 9 mm pitches | 48 |
| Number of 18 mm modules per row | 24 |
| Number of vertical modules [50 mm] | 5 |
| Standards | IEC 61439-2 IEC 61439-1 |
| Product certifications | ASEFA |
| Quantity per set | Set of 1 |
| Height | 250 mm |
| Width | 500 mm |
| Product weight | 0.92 kg |
| Material | Steel |
| Surface finish | Matt Smooth |
| Protective treatment | Electrophoresis treatment and hot-polymerised polyester epoxy powder |
| Colour | White RAL 9001 |

Environment

| | |
|-------------------------|---------------------------------|
| IK degree of protection | IK07 conforming to EN/IEC 62262 |
|-------------------------|---------------------------------|

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0701 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Produkta ietekme uz vidi |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|