



! Ierobežota  
pakalpojumu pārdošana

## Pārskats

Piegādes laiks Usually in Stock

## General

Provided equipment Rack mounting brackets  
User manual

## Physical

Cable length 2,50 m  
Colour Beige  
Depth 16,5 cm  
Height 4,4 cm  
Net weight 3 kg  
Width 43,2 cm

## Input

Permissible voltage 90...253 V  
Max line current 16 A  
Input current limits 16 A  
Load capacity 3680 VA  
Network frequency 50/60 Hz  
Plug standard IEC 60320 C20  
Input voltage 120 V  
208 V  
230 V

## Output

Number of power socket outlets 0

Number of power socket outlets	8 IEC 60320 C13
--------------------------------	-----------------

## Conformance

Product certifications	CE UL listed VCCI VDE
Standards	EN 60950 FCC part 15 class A

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0,00...15240,00 m

## Packing Units

Iepakojuma 1 svars	4,09 kg
Iepakojuma 1 augstums	7 cm
Iepakojuma 1 platums	48,3 cm
Iepakojuma 1 garums	34,3 cm
Vienību skaits iepakojumā 3	100

## Contractual warranty

Garantija	2 years repair or replace
-----------	---------------------------