



Main

Range	Canalis
Product name	KT
Product or component type	Center feeder trunking
Device short name	KTA
Device application	Feeder length
Supply	Dry-type transformer
Material	Aluminium
[Ie] rated operational current	1600 A 35 °C
Neutral position	Right
Earth conductor	Standard earth
Short-circuit level	Standard version
Provided equipment	Trunking unit

Complementary

Housing material	Polyester film
Contacts material	Copper
[Ue] rated operational voltage	1000 V
Network frequency	50/60 Hz
[Ui] rated insulation voltage	1000 V
[Icw] rated short-time withstand current	65 kA
[Ipk] rated peak withstand current	143 kA
Radiated magnetic field	0,9 µT
Thermal stress limit	4225 A².s
THDI	0...15 % 1600 A 15...33 % 2000 A 33...100 % 2500 A
Maximum voltage drop	<0,0037 V 1 50 Hz with 1A for 100 m long <0,0038 V 0,9 50 Hz with 1A for 100 m long <0,0036 V 0,8 50 Hz with 1A for 100 m long

Ir sasniegts maksimālais salīdzināmo produktu skaits. Lūdzu, atveriet sadaļu Salīdzināt produktus #SAITE# un izvēsiet kādu produktu, lai turpinātu.

<0,0034 V 0,7 50 Hz with 1A for 100 m long

Mounting mode	By screws
Mounting support	Plate
Polarity	3L + PE
Number of tap-off outlets	0
Standards	IEC 61439-6 IEC 61439-1
Dimension type	Made to measure
Connection pitch	470...700 mm
Bar width	200 mm
Depth	140 mm
Height	424 mm
Length	1 260 mm 1680 mm
Colour	White (RAL 9001)
Linear load	19 kg/m

Environment

IP degree of protection	IP55 IEC 60529
IK degree of protection	IK08 IEC 62262
Derating factor	0...35 °C 100 % of In 35...40 °C 97 % of In 40...45 °C 93 % of In 45...50 °C 90 % of In 50...55 °C 86 % of In

Packing Units

Vienību tips iepakojumā 1	PCE
Vienību skaits iepakojumā 1	1
Iepakojuma 1 svars	30,3 kg
Iepakojuma 1 augstums	34 cm
Iepakojuma 1 platums	13,8 cm
Iepakojuma 1 garums	190 cm

Offer Sustainability

Ilgspējīgs piedāvājuma statuss	Green Premium izstrādājums
REACH regula	REACH deklarācija
Nesatur REACH SVHC	Jā
ES RoHS direktīva	Atbilstīgs ES RoHS deklarācija
Nesatur toksiskus smagos metālus	Jā
Nesatur dzīvsudrabu	Jā
Informācija par RoHS izņēmumiem	Jā
Ķīnas RoHS regula	Ķīnas RoHS deklarācija Ķīnas aktīvā RoHS deklarācija (neietilpst Ķīnas RoHS juridiskajā jomā)
Vides informācijas publiskošana	Produkta ietekme uz vidi
Cirkularitātes profils	Informācija par ekspluatācijas izbeigšanu
WEEE	Eiropas Savienības tirgū no šī produkta ir jāatbrīvojas, ievērojot noteiktu atkritumu savākšanas kārtību, un produkts nedrīkst nonākt sadzīves atkritumu tvertnēs.
Nesatur PVH	Jā
Halogēnu saturs	Halogēnus nesaturošs produkts