



### Overview

Piegādes laiks	Usually in Stock
----------------	------------------

### Physical

Colour	Black
Depth	6,9 cm
Height	4,4 cm
Product weight	0,06 kg
Width	1,9 cm

### Output

Number of power socket outlets	1
--------------------------------	---

### Conformance

Product certifications	UL recognized
------------------------	---------------

### Environmental

Ambient air temperature for operation	-15...45 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0,00...3048,00 m
Storage Relative Humidity	0...95 %

### Surge Protection and Filtering

Data line protection	Cable modem/video protection
----------------------	------------------------------

#### Coaxial video/cable protection

Data line protected	1
Response time	1 ns common mode
Peak current	0,5 kA common mode 0,2 kA normal mode

#### Packing Units

Iepakojuma 1 svars	0,28 kg
Iepakojuma 1 augstums	9,9 cm
Iepakojuma 1 platums	3,3 cm
Iepakojuma 1 garums	9,5 cm
SCC14	30731304217191
Vienību skaits iepakojumā 2	96
Iepakojuma 2 augstums	206,38 mm
Iepakojuma 2 platums	412,75 mm
Iepakojuma 2 garums	638,18 mm

#### Contractual warranty

Garantija	Lifetime
-----------	----------