



Main

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	V
Product Type	Switch body

Complementary

Mounting Support	Plate Symmetrical rail
Performance Level	High performance
Number of Poles	3P
Contact Type and Composition	3 NO
Network type	DC AC
Network frequency	50/60 Hz
[Ue] IEC Rated Operational Voltage	690 V AC 50/60 Hz
IEC Rated Operational Power in W	15 kW 230...240 V AC-3) 22 kW 400...415 V AC-3) 30 kW 500 V AC-3) 30 kW 690 V AC-23A) 37 kW 500 V AC-23A) 18,5 kW 690 V AC-3) 18,5 kW 230...240 V AC-23A) 30 kW 400...415 V AC-23A)
[Ie] Rated Operational Current	57 A AC-23 Ue: 400 V
[Ith] Conventional Free Air Thermal Current	80 A
[Ithe] Conventional Enclosed Thermal Current	63 A
Making capacity (I Rms)	800 A 400 V AC-21A 800 A 400 V AC-22A

Ir sasniegts maksimālais salīdzināmo produktu skaits. Lūdzu, atveriet sadaļu Salīdzināt produktus #SAITE# un izvēsiet kādu produktu, lai turpinātu.

	800 A 400 V AC-23A
Breaking Capacity	640 A 400 V AC-21A) 640 A 400 V AC-22A) 640 A 400 V AC-23A)
Rated Conditional Short Circuit Current	10 kA 400 V 80 A aM 10 kA 400 V 80 A gG
[Icm] Rated Short Circuit Making Capacity	2,1 kA 400 V at Ipeak
Intermittent duty class	30
Suitability for isolation	Yes
[Uimp] rated impulse withstand voltage	8 kV
[Icw] rated short-time withstand Rms current	960 A 400 V 1 s
Mechanical Durability	30000 cycles
Electrical Durability	30000 cycles AC-21 30000 cycles DC-1...5
IEC Terminal Connection	Power circuit screw clamp terminals 16 mm ² flexible - with cable end Power circuit screw clamp terminals 25 mm ² solid
Tightening Torque	Power circuit 4 N.m screw clamp terminals
Height	83 mm
Width	60 mm
Depth	65 mm
Product Weight	0,5 kg

Environment

Standards	IEC 60947-3
Product Certifications	GL CSA UL
Degree of Protection	IP20 IEC 60529
Protective Treatment	TC
Mechanical Robustness	Vibrations 10...150 Hz 1 gn) IEC 60068-2-6 Shocks 11 ms 30 Gn) IEC 60068-2-27
Ambient Air Temperature for Operation	-20...50 °C
Fire Resistance	960 °C IEC 60695-2-1

Packing Units

Vienību tips iepakojumā 1	PCE
Vienību skaits iepakojumā 1	1
Iepakojuma 1 svars	292 g
Iepakojuma 1 augstums	8 cm
Iepakojuma 1 platums	8,5 cm
Iepakojuma 1 garums	12 cm
Vienību tips iepakojumā 2	S02
Vienību skaits iepakojumā 2	12
Iepakojuma 2 svars	3,796 kg
Iepakojuma 2 augstums	15 cm
Iepakojuma 2 platums	30 cm
Iepakojuma 2 garums	40 cm
Vienību tips iepakojumā 3	P06
Vienību skaits iepakojumā 3	192
Iepakojuma 3 svars	71,844 kg
Iepakojuma 3 augstums	80 cm
Iepakojuma 3 platums	80 cm

Iepakojuma 3 garums	60 cm
---------------------	-------

Offer Sustainability

Ilgspējīgs piedāvājuma statuss	Green Premium izstrādājums
REACH regula	REACH deklarācija
Nesatur REACH SVHC	Jā
ES RoHS direktīva	Atbilstīgs ES RoHS deklarācija
Nesatur toksiskus smagos metālus	Jā
Nesatur dzīvsudrabu	Jā
Informācija par RoHS izņēmumiem	Jā
Ķīnas RoHS regula	Ķīnas RoHS deklarācija Ķīnas aktīvā RoHS deklarācija (neietilpst Ķīnas RoHS juridiskajā jomā)
Vides informācijas publicēšana	Produkta ietekme uz vidi
WEEE	Eiropas Savienības tirgū no šī produkta ir jāatbrīvojas, ievērojot noteiktu atkritumu savākšanas kārtību, un produkts nedrīkst nonākt sadzīves atkritumu tvertnēs.
Nesatur PVH	Jā
Halogēnu satura veiktspēja	Halogēnus nesaturošs produkts

Contractual warranty

Garantija	18 months
-----------	-----------