



## Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCY
Product compatibility	XCKP XCKD XCMD XCKT
Associated head	ZCE05 ZCE01
Movement of operating head	Rotary
Type of operator	Roller lever spring return thermoplastic
Tracks	20/36 mm for XCMD 24/40 mm for XCKD 24/40 mm for XCKP 24/40 mm for XCKT
Type of approach	Lateral approach

## Complementary

Switch actuation	By 30° cam
Positive opening	With

## Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

## Packing Units

Iepakojuma 1 svars	0,013 kg
Iepakojuma 1 augstums	0,150 dm
Iepakojuma 1 platums	0,800 dm
Iepakojuma 1 garums	0,450 dm

## Offer Sustainability

Ilgspējīgs piedāvājuma statuss	Green Premium izstrādājums
REACH regula	<a href="#">REACH deklarācija</a>
ES RoHS direktīva	Proaktīva atbilstība (uz izstrādājumu neattiecas ES RoHS juridiskās saistības) <a href="#">ES RoHS deklarācija</a>
Nesatur dzīvsudrabu	Jā
Informācija par RoHS izņēmumiem	Jā
Vides informācijas publicēšana	<a href="#">Produkta ietekme uz vidi</a>
Cirkularitātes profils	<a href="#">Informācija par ekspluatācijas izbeigšanu</a>

## Contractual warranty

Garantija	18 months
-----------	-----------