



Principal

Product	Unidad principal central del medidor
Current Rating	125 A
Type	Fusible MGF
Bus Rating	800 A
Number of Jaws	4 without jaw release
Number of Meter Sockets	6
Bypass Type	No bypass
Socket Type	Ringed

Opcionales

Certifications	Registrado por UL
Busbar Material	Aluminium: busbar
Enclosure Material	Acero
Enclosure Rating	NEMA 3R
Maximum Voltage Rating	120 V AC
Mounting	Superficie
Phase	1 phase in 1 phase out
Wire Configuration	3-hilos
Altura	1679.45 mm
Anchura	311.15 mm
Profundidad	180.09 mm

Packing Units

Paquete 1 Peso	37.467 kg
Paquete 1 Altura	0.229 m
Paquete 1 ancho	0.373 m
Paquete 1 Largo	1.702 m

Offer Sustainability

Reglamento REACH	Declaración de REACH
Directiva RoHS UE	Conforme Declaración RoHS UE
Sin mercurio	Sí
Información sobre exenciones de RoHS	Sí
Normativa de RoHS China	Declaración RoHS China Producto fuera del ámbito de RoHS China. Declaración informativa de sustancias

Contractual warranty

Periodo de garantía	18 months
---------------------	-----------