Product datasheet

Specifications

, Green Premium[™]



1G Blank Plate, White

A3G30_WE

Main

Range	Affle Plus
Product Or Component Type	Blank plate
Colour Tint	White

Complementary

Device Mounting	Flush
Number Of Gangs	1 gang
Material	Polycarbonate: plastic part
Embedding Depth	3 mm
Width	86 mm
Height	86 mm
Depth	11 mm

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Environmental Characteristic	UV resistant

Packing Units

0	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.1 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	21.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	9.5 cm
Package 2 Width	15.0 cm
Package 2 Length	19.0 cm
Package 2 Weight	422.0 g
Unit Type Of Package 3	PAL

Number Of Units In Package 3	3840
Package 3 Height	100.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	89024.0 g

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations