



Main

Range	Affle Plus
Product or component type	Switch
Device application	Control switch
Load type	Heater Air conditioner
Colour tint	White

Complementary

Device mounting	Flush
Switch function	2-pole 2-way
Cable cross section	4 mm ² stranded cable 2.5 mm ² solid cable 2.5 mm ² stranded cable 6 x 4 mm ² solid cable for AC
Rated current	20 A at 250 V AC
Number of gangs	1 gang
Material	Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: surround Polycarbonate: actuator PA66 GF30: tip
Connections - terminals	Screw terminal
Embedding depth	22.3 mm
Width	86 mm
Height	86 mm
Depth	35.6 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Maximum ambient air temperature for operation	35 °C
Relative humidity	0...95 %
Operating altitude	5000 m
Product certifications	IEC
Standards	MS IEC 60669-1 BS EN 60669-1 IEC 60669-1

Packing Units

Package 1 Weight	112.000 g
Package 1 Height	33.000 mm
Package 1 width	86.000 mm
Package 1 Length	86.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile