



### Main

Range	Digilink
Product or component type	Wall plate
Provided equipment	With shutter
Cover plate colour tint	White

### Complementary

Number of gangs	1 gang
Communication network category	5e 6
Suitable for connector type	Ethernet network: keystone (Digilink) UTP
Shape of connector	Straight
Fixing mode	By 2 screws
Device mounting	Surface Flush
Material	ABS + PC
Width	86 mm
Length	86 mm
Targeted region	Asia Pacific.

### Environment

IP degree of protection	IP21
Ambient air temperature for operation	-10...50 °C
Ambient air temperature for storage	-10...60 °C

### Packing Units

Package 1 Weight	40.300 g
Package 1 Height	20.500 mm
Package 1 width	87.000 mm
Package 1 Length	87.000 mm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------