



Commercial status

Discontinued on: 20 July 2017

End-of-service on: 15 December 2017

E3033V2_FWWW has not been replaced. Please contact your customer care centre for more information.

Main

Range	Neo
Product or component type	Control switch
Wiring device mounting	Surface Flush
Switch function	2-way
Switch application	Switch
Load type	Fluorescent lamp Resistive Inductive Incandescent lamp
Bulb type	Fluorescent (white)
Colour tint	White

Complementary

Rated current	10 AX at 250 V AC 50/60 Hz
Number of gangs	3 gangs vertical
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding depth	23.5 mm
Depth	36 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Standards	EN 60669-1 GB 16915.1 IEC 60669-1
-----------	---

Packing Units

Package 1 Weight	86.300 g
Package 1 Height	36.000 mm
Package 1 width	87.000 mm
Package 1 Length	87.000 mm

Contractual warranty

Warranty	18 months
----------	-----------
