

Product datasheet

Specifications



Electronic Key Card Time Delay Switch, White

E8431EKT_WE

Main

Range	ZENcelo
Product or component type	Key card switch
Rated current	16 A at 240 V AC
Colour tint	White

Complementary

Device mounting	Surface Flush
Connections - terminals	Brass terminal
Clamping connection capacity	3 x 4 mm ² for solid cable(s) 3 x 4 mm ² for stranded cable(s) 2 x 2.5 mm ² for solid cable(s) 2 x 2.5 mm ² for stranded cable(s)
Embedding depth	29.1 mm
Width	87.2 mm
Height	87.2 mm
Depth	41.1 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Ambient air temperature for storage	0...60 °C
Standards	GB 16915.2 IEC 60669-2-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm

Package 1 Weight	166.17 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	6 cm
Package 2 Weight	1.106 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	9970.2 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)