

# Product datasheet

Specifications



## Panic Button with Key Reset, Sliver Bronze

E8431KPB\_SZ

### Main

Range	ZENcelo
Product or component type	EMO switch

### Complementary

Device mounting	Surface Flush
Cable cross section	1.5 mm <sup>2</sup>
Rated current	3 A at 24 V DC
Material	Polycarbonate
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	33.6 mm

### Environment

Maximum ambient air temperature for operation	30 °C
Relative humidity	0...95 %

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	102.54 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm

Package 2 Weight	1.02 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	10703.2 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)