

Product datasheet

Specifications



2 Gang Switch w/Illuminated "DoNotDisturb&PleaseCleanUp" Symbols, Silver White

E8432DMS_SW

⚠ Discontinued on: 23 Jan 2021

⚠ Discontinued

Main

Range	ZENcelo
Product Or Component Type	Switch
Device Application	Bell switch
Load Type	Resistive Inductive lamp
Colour Tint	Silver white
Cover Frame Colour Tint	Silver white

Complementary

Device Mounting	Flush Surface
Rated Current	10 A at 250 V AC 50/60 Hz
Local Signalling	Please clean up: indicator light, neon (green) Do not disturb: indicator light, neon (orange)
Number Of Gangs	2 gangs
Material	Brass: contact Polycarbonate: base Polycarbonate: cover Polycarbonate: grid plate Polycarbonate: surround
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	27.72 mm

Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	2000 m
Standards	IEC 60669-1 GB 16915.1 MS IEC 60669-1 BS EN 60669-1

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	113.8 g

Contractual warranty

Warranty	18 months
----------	-----------