

# Product datasheet

Specifications



## ESM 15A 250V surface mount switched socket

ESM15\_15\_G11

### Main

Range	S-Classic
Product or component type	Switched socket
Device application	Power supply
Outlet poles configuration	2P + E with shutter
Rated current	15 A at 250 V AC 50/60 Hz

### Complementary

Device presentation	Complete product
Number of gangs	1 gang
Device mounting	Surface
Material	Plate: PC (polycarbonate), white Dolly: PC (polycarbonate), white Base: PP (polypropylene), black
Height	87 mm
Width	87 mm
Depth	47 mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	SS 145 MS 589 BS 1363

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.4 cm
Package 1 Width	8.2 cm
Package 1 Length	5.0 cm
Package 1 Weight	250.0 g

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Mercury free</b>	Yes
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
<b>RoHS exemption information</b>	Yes
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>

### Recommended replacement(s)