

Product datasheet

Specifications



1 Gang Category 6 Data Outlet with Shutter

KB31RJ6_WE

Training Objectives : Will be Compliant

Main

Range	Vivace
Device short name	KB31
Product or component type	Data socket with shutter
Device application	Communication
Device presentation	Complete mechanism
Cover frame colour tint	White

Complementary

Communication network category	6
Number of gangs	1 gang
Tightening torque	0.4 N.m
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Width	86 mm
Height	86 mm
Projecting depth	8 mm
Embedding depth	35 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	FCC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	83.7 g
Package 1 Height	8.6 cm
Package 1 Width	5.0 cm
Package 1 Length	8.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	907.0 g
Package 2 Height	15.0 cm
Package 2 Width	19.0 cm
Package 2 Length	10.0 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	8620.0 g
Package 3 Height	315.0 mm
Package 3 Width	500.0 mm
Package 3 Length	500.0 mm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)

Recommended replacement(s)