Product datasheet



12 CHANNEL RELAY DIN LEARN



L5512RVF

Main

Range	C-Bus
Product Brand	Clipsal

Complementary

•	
[Us] Rated Supply Voltage	1536 V DC
Network Type	AC/DC
Device Composition	Socket-outlet Socket-outlet
Connector Type	Screw terminals
Width	215 mm
Height	85 mm
Depth	65 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.788 cm
Package 1 Width	10.613 cm
Package 1 Length	22.681 cm
Package 1 Weight	710 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	222 cm
Package 2 Width	246 cm
Package 2 Length	348 cm
Package 2 Weight	4.82 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Toxic Heavy Metal Free	
	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information