



## PratiKa wander plug - straight - 32 A - 3P + E - 380...415 V AC - IP67

PKX32M734

#### Main

Range	Mureva
Product Or Component Type	Wander plug
Device Short Name	Mureva plug
Plug, Socket Category	Low voltage
Poles Description	3P+E
Network Type	AC
Outlet Standard	Industrial

### Complementary

Plug, Socket, Control Station Shape	Straight
[In] Rated Current	32 A
[Ue] Rated Operational Voltage	380415 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	6 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Sleeves: brass
Connections - Terminals	Fast connection
Cable Cross Section	2.56 mm <sup>2</sup>
Cable Outer Diameter	11.521 mm
Cable Entry	Cable gland Fair lead
Thread Type	Pg 21
Height	152 mm
Width	95 mm
Depth	95 mm
Colour	Grey (RAL 7035)
Voltage Colour	Red

#### **Environment**

Standards	IEC 60309-1 IEC 60309-2
Ip Degree Of Protection	IP67 conforming to IEC 60529

Ik Degree Of Protection	IK08 conforming to EN 62262
Fire Resistance	850 °C conforming to IEC 60695-2-11
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	35 °C ( 86400 s ) -2540 °C

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.3 cm
Package 1 Width	9.4 cm
Package 1 Length	16.8 cm
Package 1 Weight	272 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	18.2 cm
Package 2 Width	26.8 cm
Package 2 Length	26.8 cm
Package 2 Weight	1.8 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	12
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.087 kg

# **Contractual warranty**

Warranty 18 months



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations