

Product datasheet

Specifications



Actassi CL-C5e CP Cabling F/UTP Cat5e LSZH DPM 10.0m

VDICP3501001

⚠ Discontinued on: 30 Jun 2023

⚠ Discontinued

Main

Range	Actassi
Product Or Component Type	Consolidation point link
Colour	CP link: green (RAL 6016)
Quantity Per Set	1 piece

Complementary

Device Composition	RJ45 plug STP S-One DPM RJ45 STP Cable F/UTP
Communication Network Category	5e
Communication Network Type	1000BASE-TX
Transmission Frequency	155 MHz
Input Impedance	100 Ohm
Connector Type	RJ45
Material	: jacket
Length	10 m
Targeted Region	Europe

Environment

Ambient Air Temperature For Operation	0...60 °C
Ambient Air Temperature For Storage	-15...60 °C
Ambient Air Temperature For Installation	-5...40 °C
Temperature Resistance	60 °C
Environmental Characteristic	: S-One DPM network socket

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	30.0 cm
Package 1 Length	30.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	450.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	15
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	8.3 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
