Product datasheet

Specifications

 → Green Premium[™]



FRONT PLATE NSX/CVS 630 VERTICAL FIXED ROTARY HANDLE W300 12M

03283

- () Discontinued on: 30 Sept 2022
- (!) End-of-service on: 25 Apr 2023

Main

Range	Prisma
Range Of Product	Prisma G Prisma P
	Front plate
	r toni plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G duct
	Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed NSX400 without earth leakage protection - control: toggle - vertical installation
	EasyPact: fixed CVS400 without earth leakage protection - control: direct front rotary
	handle - vertical installation
	EasyPact: fixed CVS630 without earth leakage protection - control: direct front rotary handle - vertical installation
	ComPact: fixed NSX400 without earth leakage protection - control: direct front rotary
	handle - vertical installation
	ComPact: plug-in NSX400 without earth leakage protection - control: toggle - vertical installation
	ComPact: fixed NSX400 without earth leakage protection - control: motor mechanism
	- vertical installation
	ComPact: plug-in NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation
	ComPact: plug-in NSX400 without earth leakage protection - control: motor
	mechanism - vertical installation
	ComPact: fixed NSX630 without earth leakage protection - control: toggle - vertical
	installation ComPact: fixed NSX630 without earth leakage protection - control: direct front rotary
	handle - vertical installation
	ComPact: plug-in NSX630 without earth leakage protection - control: toggle - vertical
	installation
	ComPact: fixed NSX630 without earth leakage protection - control: motor mechanism - vertical installation
	ComPact: plug-in NSX630 without earth leakage protection - control: direct front
	rotary handle - vertical installation
	ComPact: plug-in NSX630 without earth leakage protection - control: motor
	mechanism - vertical installation
Poles Description	1 x 4P: mounting plate support: NSX400 vertical installation
	1 x 3P: mounting plate support: CVS400 vertical installation
	1 x 4P: mounting plate support: CVS400 vertical installation
	1 x 3P: mounting plate support: CVS630 vertical installation 1 x 4P: mounting plate support: CVS630 vertical installation
	1 x 3P: mounting plate support: NSX400 vertical installation
	1 x 3P: mounting plate support: NSX630 vertical installation
	1 x 4P: mounting plate support: NSX630 vertical installation
Operating Position	Vertical

Complementary

Life Is On Schneider

Enclosure/Cubicle Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm	
Connection Position	Direct connection Front connection	
Number Of Vertical Modules [50 Mm]	12	
Standards	IEC 61439-2 IEC 61439-1	
Product Certifications	ASEFA	
Material	Steel	
Surface Finish	Smooth Matt	
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Colour	White (RAL 9001)	
Height	600 mm	
Width	300 mm	
Net Weight	1.24 kg	
Quantity Per Set	Set of 1	

Functional Unit

400 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed toggle vertical 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed toggle vertical 4P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed direct front rotary handle vertical 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed direct front rotary handle vertical 4P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed motor mechanism vertical 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed motor mechanism vertical 4P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in toggle vertical 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in toggle vertical 4P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in direct front rotary handle vertical 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in direct front rotary handle vertical 4P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in motor mechanism vertical 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in motor mechanism vertical 4P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed toggle vertical 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed toggle vertical 4P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed direct front rotary handle vertical 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed direct front rotary handle vertical 4P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed motor mechanism vertical 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed motor mechanism vertical 4P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in toggle vertical 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in toggle vertical 4P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in direct front rotary handle vertical 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in direct front rotary handle vertical 4P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in motor mechanism vertical 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in motor mechanism vertical 4P 1 front connection 12 300 mm Prisma G floor-standing duct EasyPact CVS400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 300 mm Prisma G wall-mounted duct EasyPact CVS400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 300 mm Prisma G floor-standing duct EasyPact CVS400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 300 mm Prisma G wall-mounted duct EasyPact CVS400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 300 mm Prisma G floor-standing duct EasyPact CVS630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 300 mm Prisma G wall-mounted duct EasyPact CVS630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 300 mm Prisma G floor-standing duct EasyPact CVS630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 300 mm Prisma G wall-mounted duct EasyPact CVS630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 300 mm Prisma G floor-standing duct ComPact NSX400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 300 mm Prisma G wall-mounted duct ComPact NSX400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 300 mm Prisma G floor-standing duct ComPact NSX400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 300 mm Prisma G wall-mounted duct ComPact NSX400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 300 mm Prisma G floor-standing duct ComPact NSX630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 300 mm Prisma G wall-mounted duct ComPact NSX630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 300 mm Prisma G floor-standing duct ComPact NSX630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 300 mm Prisma G wall-mounted duct ComPact NSX630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	26.000 cm
Package 1 Length	61.000 cm
Package 1 Weight	1.200 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	17.000 cm
Package 2 Width	54.000 cm
Package 2 Length	82.000 cm
Package 2 Weight	13.250 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	40
Package 3 Height	49.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	54.800 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile