

Product datasheet

Specifications



Acti9 - IH - mechanical time switch - 24 hours + 7 days - 150 h memory

15366

! Discontinued on: 23 Jan 2021

! Discontinued

Price: 148,172.73 NGN

Main

Range Of Product	Acti9
Product Name	Acti9 IH
Device Short Name	IH
Product Or Component Type	Mechanical time switch
Number Of Channels	2
Function Available	Manual time changeover

Complementary

Device Application	Building
Load Type	Parallel-corrected fluorescent tube 1 x conventional ballast 58 W Non-corrected fluorescent tube 10 x conventional ballast 58 W Serial-corrected fluorescent tube 10 x conventional ballast 58 W Non-corrected fluorescent tube 15 x conventional ballast 40 W Serial-corrected fluorescent tube 15 x conventional ballast 40 W Parallel-corrected fluorescent tube 2 x conventional ballast 40 W 230 V AC halogen lamp 1100 W 230 V AC incandescent lamp 1100 W Dual mounted fluorescent tube 3 x conventional ballast 2 x 100 W Dual mounted fluorescent tube 5 x conventional ballast 2 x 58 W Non-corrected fluorescent tube 6 x conventional ballast 100 W Serial-corrected fluorescent tube 6 x conventional ballast 100 W
Cycle Duration	24 hours + 7 days
Maximum Number Of Switchings	16 on - 16 off + 7 on - 7 off
Minimum Interval Duration	45 min + 12 h
Type Of Setting	Manual time changeover
Measurement Accuracy	+/- 1 s/day 20 °C
Power Consumption In Va	2.5 VA
Maximum Switching Current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] Rated Operational Voltage	230 V AC - 15...10 % at 50 Hz
Battery Life	6 year(s)
Backup Time	150 h time and program saving
Mounting Support	DIN rail
9 Mm Pitches	6
Colour Tint	White (RAL 9003)
Connections - Terminals	Screw terminals

Width	54 mm
Height	82 mm
Depth	66 mm
Net Weight	0.223 kg

Environment

Ambient Air Temperature For Operation	-20...55 °C
Ip Degree Of Protection	Terminals: IP20 B

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	8 cm
Package 1 Length	10.5 cm
Package 1 Weight	240 g

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu RoHS Directive Compliant with Exemptions

China RoHS Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)