Product datasheet

Specification





PratiKa industrial socket - 125 A - 3P + E - 200...250 V AC - IP67

81691

Price: 176,042.05 NGN

Main

Range	Mureva
Product Or Component Type	Socket
Device Short Name	Mureva socket
Plug, Socket Category	Low voltage
Poles Description	3P+E
Network Type	AC
Outlet Standard	Industrial

Complementary

Mounting Mode	Panel-mounted	
Plug, Socket, Control Station Shape	Straight	
[In] Rated Current	125 A	
[Ue] Rated Operational Voltage	200250 V	
Network Frequency	50/60 Hz	
Ground Lug Clockwise Position	9 h	
Plug, Socket Material	Housing: self-extinguishing engineering polymer	
Contacts Material	Pins: stainless steel Sleeves: nickel plated brass Springs: stainless steel	
Connections - Terminals	Captive screws, completely loosened	
Cable Cross Section	1670 mm²	
Net Weight	1.17 kg	
Base Dimension	110 x 114 mm	
Height	114 mm	
Width	129 mm	
Depth	161 mm	
Colour	Grey (RAL 7035)	
Voltage Colour	Blue	

Environment

Standards	EN 60309-1 EN 60309-2
Ip Degree Of Protection	IP67 conforming to IEC 60529

Ik Degree Of Protection	IK08 conforming to EN 62262
Fire Resistance	850 °C conforming to IEC 60695-2-11
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient Air Temperature For Operation	35 °C (86400 s)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	11.0 cm
Package 1 Length	16.1 cm
Package 1 Weight	1.19 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations