# **Product datasheet**

Specifications





### INSULATED DOUBLE CABLE END MEDIUM SIZE 0.75 MM<sup>2</sup> GREY

AZ5DE007D

#### Price: 11,944.94 NGN

#### Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	DIN 46228-4
Type Of Packing	Dispenser pack
Quantity Per Set	5 sets of 100
Cable Cross Section	0.75 mm <sup>2</sup>

# Complementary

Cable End Type	Twin conductor
Additional Information	Without marker tag holder
Colour	Blue
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	2
Awg Gauge	AWG 20
Bezel Size	Ø 2.8 x 5 mm
Tube Diameter	2 mm
Length	15 mm
Tube Length	8 mm
Net Weight	0.13 kg

#### Environment

Product Certifications	cCSAus
Ambient Air Temperature For Operation	-20105 °C

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm
Package 1 Length	1.400 cm

Package 1 Weight	0.100 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	500
Package 2 Height	13.000 cm
Package 2 Width	7.000 cm
Package 2 Length	12.600 cm
Package 2 Weight	126.000 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	5000
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	1.605 kg

# **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Circularity Profile	No need of specific recycling operations
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Reach Regulation	REACh Declaration