Product datasheet

Specifications





Acti9 - IH - mechanical time switch - 24 h - 150 h memory

CCT15365

Price: 120,000.00 NGN

Main

Range Of Product	Acti9
Product Name	Acti9 IH
Device Short Name	IH
Product Or Component Type	Mechanical time switch
Number Of Channels	1
Function Available	Manual time changeover

Complementary

Complementary		
Device Application	Building	
Load Type	230 V AC halogen lamp 1000 W 230 V AC incandescent lamp 1100 W 230 V AC fluocompact lamp 600 VA Parallel-corrected fluorescent tube 2 x electronic ballast 40 W 12 μF Compact fluorescent lampelectronic ballast 25 W LED lamp < 2 W 20 W LED lamp > 2 W 180 W	
Cycle Duration	24 h	
Maximum Number Of Switchings	48 on - 48 off	
Minimum Interval Duration	15 min	
Type Of Setting	Manual time changeover	
Measurement Accuracy	+/- 1 s/day 20 °C	
Power Consumption In W	0.5 W	
Maximum Switching Current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6	
[Ue] Rated Operational Voltage	110230 V AC at 5060 Hz	
[Uimp] Rated Impulse Withstand Voltage	4 KV	
Battery Life	6 year(s)	
Backup Time	150 h time and program saving 230 V AC 75 h time and program saving 110 V AC	
Mounting Support	DIN rail	
9 Mm Pitches	6	
Colour Tint	White (RAL 9003)	
Connections - Terminals	Screwless terminals	
Clamping Connection Capacity	2 x 0.52 .5 mm ²	
Width	54 mm	

Height	90 mm
Depth	66 mm
Net Weight	0.198 kg
Standards	EN 60730-1

Environment

Ambient Air Temperature For Operation	-2055 °C
Pollution Degree	2
Ip Degree Of Protection	IP20 conforming to EN 60529

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	6.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	152.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	36
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.943 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information