



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	User manual
--------------------	-------------

Physical

Cable end 2	RJ45 female Cat Cat 6 Straight Through
Height	11.4 cm
Cable length	6.40 m
Cable end 1	RJ45 female Cat Cat 6 Straight Through
Depth	34.3 cm
Net weight	2.36 kg
Width	34.3 cm

Output

Number of port	6
----------------	---

Conformance

Product certifications	TAA compliance UL listed UL recognized
------------------------	--

Environmental

Storage Relative Humidity	0...95 %
Storage altitude	0.00...3048.00 m
Ambient air temperature for operation	-15...45 °C

Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C

Packing Units

Package 1 Weight	2.8 kg
Package 1 Height	11.4 cm
Package 1 width	34.3 cm
Package 1 Length	34.3 cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------