

# Product datasheet

Specifications



## ZENcelo-16AX 2 Gang 2 Way Full-Flat Switch with Ondicat w/Blister-Silver Bronze

E8432\_2\_SZ

**Price : 5,692.89 NGN**

### Main

Range	ZENcelo
Product or component type	Switch
Load type	Incandescent lamp Resistive Fluorescent lamp Inductive
Colour tint	Silver bronze
Cover frame colour tint	Silver bronze

### Complementary

Device mounting	Flush Surface
Switch function	2-way
Rated current	20 A at 250 V AC 50/60 Hz
Local signalling	Mechanical indicator (amber)
Number of gangs	2 gangs
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround
Connections - terminals	Brass rod terminals
Width	87 mm
Height	87 mm
Depth	31 mm

### Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	EN 60669-1 SS 227-1 GB 16915.1 MS IEC 60669-1

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	148.26 g
Unit Type of Package 2	S04
Number of Units in Package 2	80
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	8.418 kg
Unit Type of Package 3	P12
Number of Units in Package 3	1600
Package 3 Height	125 cm
Package 3 Width	105 cm
Package 3 Length	80 cm
Package 3 Weight	169.96 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Recommended replacement(s)