Product datasheet

Specification





45A Double Pole Switch and 13A Switched Socket Outlet, Silver Bronze

E84T15D45N_SZ

Price: 42,613.64 NGN

Main

Range	ZENcelo
Product Or Component Type	Power socket-outlet
Load Type	No inductive load
Cover Frame Colour Tint	Silver bronze
Cover Plate Colour Tint	Bronze

Complementary

Device Mounting	Flush Surface
Switch Function	2-pole
Rated Current	45 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Material	Control circuit: polycarbonate surround Brass contact Phosphor contact Polycarbonate base Polycarbonate grid plate
Connections - Terminals	Folded terminal
Width	147 mm
Height	87 mm
Depth	8 mm

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Environmental Characteristic	UV resistant indoor use
Operating Altitude	2000 m
Standards	BS 4177
Standards	BS 4177

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm

Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	244.603 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	50
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	10.161 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	1000
Package 3 Height	125 cm
Package 3 Width	105 cm
Package 3 Length	80 cm
Package 3 Weight	204.813 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations