

Product datasheet

Specifications



45A Double Pole Switch and 13A Switched Socket Outlet, Silver Bronze

E84T15D45N_SZ

Price : 15,207.03 NGN

Main

Range	ZENcelo
Product or component type	Power socket-outlet
Load type	No inductive load
Cover frame colour tint	Silver bronze
Cover plate colour tint	Bronze

Complementary

Device mounting	Flush Surface
Switch function	2-pole
Rated current	45 A at 250 V AC 50 Hz
Number of gangs	1 gang
Material	Control circuit: polycarbonate surround Brass contact Phosphor contact Polycarbonate base Polycarbonate grid plate
Connections - terminals	Folded terminal
Width	147 mm
Height	87 mm
Depth	8 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	BS 4177 BS 4177

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	244.603 g
Unit Type of Package 2	S04
Number of Units in Package 2	50
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	10.161 kg
Unit Type of Package 3	P12
Number of Units in Package 3	1000
Package 3 Height	125 cm
Package 3 Width	105 cm
Package 3 Length	80 cm
Package 3 Weight	204.813 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)