



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Installation guide Toolless mounting kit Vertical mounting brackets
--------------------	---

Physical

Cable length	3.00 m
Colour	Black
Depth	6.2 cm
Height	173.8 cm
Net weight	7.9 kg
Width	5.5 cm

Input

Input current limits	32 A
Load capacity	7360 VA
Network frequency	50/60 Hz
Plug standard	IEC 60309 32 A 2P + E
Input voltage	200 V 208 V 230 V

Output

Number of power socket outlets	20 IEC 60320 C13 4 IEC 60320 C19
--------------------------------	-------------------------------------

Conformance

Product certifications	CE EAC TÜV
------------------------	------------------

Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Weight	9 kg
Package 1 Height	195 cm
Package 1 width	16 cm
Package 1 Length	11 cm

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------
