
# **Product datasheet**

Specifications





# Switched Socket, Vivace, 13A, 250V, 1 gang, white

KB15

Price: 3,715.91 NGN

#### Main

Range	Vivace
Product Or Component Type	Switched socket
Device Short Name	KB15
Device Application	Power supply
Device Presentation	Complete product
Switch Application	On/off switching
Main Colour Tint	White
Colour Tint	White

### Complementary

Joinplomontal y	
Outlet Poles Configuration	2P + E
Number Of Gangs	1 gang
Colour Tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm
Embedding Depth	22.0 mm
Rated Current	13 A at 250 V AC, resistive
Network Frequency	50/60 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	Pillar terminal
Terminal Identifier	N Earth L
Tightening Torque	0.4 N.m
Clamping Connection Capacity	2 x 4 mm <sup>2</sup> 3 x 2.5 mm <sup>2</sup>
Width	87 mm
Height	87 mm

Depth	35 mm

#### **Environment**

Standards	MS 589 SS 145
	BS 1362-2
Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For Storage	-560 °C
Relative Humidity	095 %
Operating Altitude	<= 2000 m
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	110 g

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations