Product datasheet

Specifications





Vivace 13A 250V 1Gang DP Large Dolly Switched socket with NE, Aluminium silver

KB15LDN_AS

() Discontinued on: 30 Jun 2023

() Discontinued

Main

| Range | Vivace |
|---------------------------|------------------|
| Product Or Component Type | Switched socket |
| Device Short Name | KB15 |
| Device Application | Power supply |
| Device Presentation | Complete product |
| Main Colour Tint | Aluminium silver |
| Colour Tint | Aluminium silver |

Complementary

| Pilot Light | Red neon indicator |
|------------------------------|---|
| Outlet Poles Configuration | 2P + E |
| Number Of Gangs | 1 gang |
| Colour Tint | Aluminium silver |
| Material | Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base |
| Projecting Depth | 8 mm |
| Device Mounting | Flush |
| Mounting Support | Wall mounted |
| Fixing Mode | By screw M3.5 |
| Fixing Center | 60.3 mm |
| Embedding Depth | 35 mm |
| Rated Current | 13 A at 250 V AC, no inductive load |
| Network Frequency | 50 Hz |
| Contacts Material | Brass and phosphor bronze |
| Connections - Terminals | Pillar terminal |
| Terminal Identifier | N L Earth |
| Tightening Torque | 0.4 N.m |
| Clamping Connection Capacity | 2 x 4 mm² 3 x 2.5 mm² |
| Width | 86 mm |

| Height | 86 mm |
|--------|-------|
| Depth | 35 mm |

Environment

| Standards | SS 145 BS 1362-2 MS 589 |
|--|-------------------------------|
| Ambient Air Temperature For Operation | -540 °C |
| Relative Humidity | 095 % |
| Environmental Characteristic | Indoor use |

Packing Units

| • | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.6 cm |
| Package 1 Width | 3.2 cm |
| Package 1 Length | 8.6 cm |
| Package 1 Weight | 114 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 9.5 cm |
| Package 2 Width | 15 cm |
| Package 2 Length | 19 cm |
| Package 2 Weight | 1.21 kg |
| Unit Type Of Package 3 | CAR |
| Number Of Units In Package 3 | 100 |
| Package 3 Height | 21 cm |
| Package 3 Width | 31.5 cm |
| Package 3 Length | 50 cm |
| Package 3 Weight | 11651 g |
| | |

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |