Product datasheet

Specification





13A 250V Twin Gang Switched Socket with Neon

KB25N

Price: 9,136.36 NGN

Main

Range	Vivace
Product Or Component Type	Switched socket
Device Short Name	KB25
Device Application	Power supply
Device Presentation	Complete product
Switch Application	On/off switching
Main Colour Tint	White
Colour Tint	White

Complementary

Complementary	
Pilot Light	Red neon indicator
Outlet Poles Configuration	2P + E
Number Of Gangs	2 gangs
Colour Tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	120.6 mm
Embedding Depth	22.0 mm
Rated Current	13 A at 250 V AC, resistive
Network Frequency	50/60 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	Pillar terminal
Terminal Identifier	L N Earth
Tightening Torque	0.4 N.m
Clamping Connection Capacity	2 x 4 mm ² 3 x 2.5 mm ²
Width	147 mm

Height	87 mm
Depth	35 mm

Environment

Standards	MS 589 SS 145 BS 1363
Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For Storage	-560 °C
Relative Humidity	095 %
Operating Altitude	<= 2000 m
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.0 cm
Package 1 Width	31.5 cm
Package 1 Length	50.0 cm
Package 1 Weight	175.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	21.0 cm
Package 2 Width	31.5 cm
Package 2 Length	50.0 cm
Package 2 Weight	8750.0 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations