

# Product datasheet

Specifications



## Twin Gang Blank Plate



KBT30\_WE

**Price : 1,635.60 NGN**

### Main

Range	Vivace
Product or component type	Blank plate
Device short name	KBT30

### Complementary

Number of gangs	2 gangs
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround
Projecting depth	8 mm
Device mounting	Flush
Width	146 mm
Height	86 mm

### Environment

Standards	BS 5733
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	8.6 cm
Package 1 Length	25.3 cm
Package 1 Weight	103 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	15 cm
Package 2 Width	38 cm
Package 2 Length	10 cm
Package 2 Weight	1.195 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	10550 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Recommended replacement(s)