Product datasheet

Specification





ClimaSys CC - simple thermostat 250V - range of temperature 0... 60°C - NO - °C

NSYCCOTHO

Price: 29,366.59 NGN

Main

Range	ClimaSys
Product Name	ClimaSys CC
Product Or Component Type	Simple thermostat
Temperature Setting Range	00° °C
Information Displayed	Temperature in °C

Complementary

Complementary	
Input Voltage	250 V
Sensor Type	Bimetal
Contacts Type And Composition	NO
Contact Resistance	10 mOhm
Service Life In Cycles	100000 cycles
Maximum Switching Capacity	2 A 120250 V AC inductive pf: 0.6 10 A 250 V AC resistive 15 A 120 V AC resistive 30 W DC
Electrical Connection	4 terminals, clamping capacity: 2.5 mm²
Mounting Mode	Clipped
Height	External: 68 mm
Width	External: 33 mm
Depth	44 mm external:
Net Weight	40 g
Mounting Location	35 mm DIN rail On mounting plate Cross rails Spacial upright
Ambient Air Temperature For Operation	-2080 °C
Ip Degree Of Protection	IP20
Hysteresis	7 K +/- 0.4K
Number Of Outputs	1 ventilation function
Material	PC
Colour	Light grey
Flame Retardance	Self-extinguishing conforming to UL94 (material V0)
Product Certifications	UL

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	6.0 cm
Package 1 Length	8.0 cm
Package 1 Weight	64.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	24.0 cm
Package 2 Width	33.0 cm
Package 2 Length	41.0 cm
Package 2 Weight	7.588 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	3600
Package 3 Height	166.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	280.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations