# **Product datasheet**

Specification





Spacial CRN plain door w/o mount.plate. H400xW300xD200 IP66 IK10 RAL7035..

NSYCRN43200

Price: 130,531.71 NGN

#### Main

Range	Spacial
Product Name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	400 mm
Enclosure Nominal Width	300 mm
Enclosure Nominal Depth	200 mm
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 cable gland plate 1 door 1 lock
Door Type	Plain
Mounting Plate Description	Without mounting plate

## Complementary

Body Type	Sides made from a single folded section  Back welded with double profile forming a protected sealed area
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 mm double-bar lock
Type Of Gland Plate	Standard
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Body: steel
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	UL cUL DNV-GL
Net Weight	5.81 kg

#### **Environment**



Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IFC 62262

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.000 cm
Package 1 Width	31.000 cm
Package 1 Length	41.500 cm
Package 1 Weight	5.569 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	64
Package 2 Height	220.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	369.416 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations