Product datasheet

Specifications





Spacial S3D plain door with mount.plate. H600xW400xD200.IP66 IK10 RAL7035.

NSYS3D6420P

Price: 451,856.76 NGN

Main

····a···		
Range	Spacial	
Product Name	Spacial S3D	
Application	Multi-purpose	
Category	Compact enclosure	
Enclosure Nominal Height	600 mm	
Enclosure Nominal Width	400 mm	
Enclosure Nominal Depth	200 mm	
Door Type	Plain	
Mounting Plate Description	Plain	
Type Of Gland Plate	Standard	
Installation Accessory Type	Wall-mounting	
Device Composition	body mounting plate door with lock cable gland plate	

Complementary

Body Type	Single piece body Gutter-shaped front rail double sheet thickness	
Number Of Doors	Front face: 1 door(s)	
Door Opening Side	Reversible (120 °)	
Lock Type	3 points lock, 3 mm double-bar	
Accessibility For Operation	Front	
Removable Parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element	
Material	Enclosure: steel Mounting plate: galvanised steel	
Surface Finish	Enclosure: epoxy-polyester powder	
Colour	Enclosure: grey (RAL 7035)	
Standards	IEC 62208	

Product Certifications	LR GL UL cUL DNV		
	BV		
Net Weight	13 kg		

Environment

Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP66 conforming to IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.5 cm
Package 1 Width	42.0 cm
Package 1 Length	61.5 cm
Package 1 Weight	13.306 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	30
Package 2 Height	199.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	411.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	