



Commercial status

Discontinued on: 23 January 2021

End-of-service on: 24 January 2021

⚠ To be discontinued

Main

Range	Dardo Plus
Product or component type	Control unit
Device application	Control
Function	Addressable
Supply	Rechargeable internal battery
Language	German Italian Romanian French Spanish English Portuguese

Complementary

[Ue] rated operational voltage	220 V 50 Hz
Power consumption in VA	2 VA
Rated voltage	6 V 0.8 Ah Ni-Cd (Nickel-Cadmium) battery
Autonomy	0.5...1 h depending on the number of lights connected
Charging time	24 s
Output type	Line 1 <1000 m
Operating distance	2 200 m with 1 mm ² 100 2 400 m with 1.5 mm ² 100 2 600 m with 2.5 mm ² 100

Packing Units

Package 1 Weight	1.422 kg
Package 1 Height	1.180 dm
Package 1 width	2.570 dm
Package 1 Length	3.680 dm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------