

Product datasheet

Specifications



InfraStruxure PDU 60kW 400V/400V

PD60H5HK1

⚠ Discontinued on: 25 May 2023

⚠ End-of-service on: 18 Oct 2023

⚠ Discontinued

Overview

Presentation	Designed to increase flexibility and agility of data center power distribution through a design that does not require a raised floor.
Lead Time	Usually Ships within 3 Weeks

Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	230 V 400 V 3 phases
Number Of Cables	1
Provided Equipment	Installation guide User manual

Physical

Colour	Black
Height	215.9 cm
Width	60 cm
Depth	91.4 cm
Net Weight	410 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Network Frequency	50 Hz +/- 3 Hz
Input Current Limits	167 A
Load Capacity	60000 VA

Output

Efficiency	98 %
------------	------

Conformance

Product Certifications	UL listed
------------------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...9144.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	218.4 cm
Package 1 Width	121.9 cm
Package 1 Length	91.4 cm
Package 1 Weight	454.56 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------